

Product Code . JL-S-2071

Rotary Shaker



Description

Rotary Shaker (Platform Type)

Body made out of thick mild steel sheet finished in staving enamel paint heavy-duty motors of suitable capacities are provided for long time, continuous operation.

Fixed speed and variable speed models are offered.

Platform provided with rubber discs or wire partitions to hold flasks.

To work on 220V AC to 50 Hz single phase.

Optional:- 0-60 minutes timer.

Platform	Size	Holding Cap	Motor HP
----------	------	-------------	----------

45x45 cm	25 flasks of 100 ml	0.25
----------	---------------------	------

55x55cm	25 Flask of 250 ml	0.25
---------	--------------------	------

90x90cm	49 flaks of 250 ml	0.25
---------	--------------------	------

100x100cm	81 flasks of 500 ml	1
-----------	---------------------	---

Rotary Shaker Manufacturer, Rotary Shaker Suppliers, Rotary Shaker India, Rotary Shaker Exporter, buy Rotary Shaker, Shaker, Rotary Shaker, Analytical Research Equipments, buy Rotary Shaker Online India

```
{ "@context": "http://schema.org/", "@type": "Product", "name": "Rotary Shaker", "image":  
"https://www.jlabexport.com/images/catalog/product/1848403796rotary-shaker.jpg", "description":  
"Rotary Shaker (Platform Type) Body made out of thick mild steel sheet finished in staving enamel  
paint heavy-duty motors of suitable capacities are provided for long time, continuous operation. Fixed  
speed and variable speed models are offered. Platform provided with rubber discs or wire partitions  
to hold flasks. To work on 220V AC to 50 Hz single phase. Optional:- 0-60 minutes timer. Platform  
Size Holding Cap Motor HP 45x45 cm 25 flasks of 100 ml 0.25 55x55cm 25 Flask of 250 ml 0.25  
90x90cm 49 flaks of 250 ml 0.25 100x100cm 81 flasks of 500 ml 1 Rotary Shaker Manufacturer,  
Rotary Shaker Suppliers, Rotary Shaker India, Rotary Shaker Exporter, buy Rotary Shaker, Shaker,  
Rotary Shaker, Analytical Research Equipments, buy Rotary Shaker Online India", "brand": "JLab  
Export", "sku": "5", "gtin8": "5", "gtin13": "5", "gtin14": "5", "mpn": "5", "aggregateRating": { "@type":  
"AggregateRating", "ratingValue": "5", "bestRating": "5", "worstRating": "0", "ratingCount": "5" } }
```
