



Product Code . JL-WDP-3928

Rotary Vacuum Evaporator

Description

Rotary Vacuum Evaporator

The apparatus consists of an evaporating flask rotated by heavy duty motor in a heating water bath.

Fitted with speed regulator for minor speed adjustments.

Vacuum distillation of solvent at high and low temperature is achieved quickly by use of a heavy duty motor, which prevents foaming and bumping of the liquid (solvent) into the evaporating flask and also distillation under controlled atmosphere.

The evaporating flask is pear shaped to give a large surface area of evaporation. Evaporating flask is clamped to a glass duct which goes through the drive unit and protrudes about 120mm into the condenser..

Condenser is fitted with standard joint at the top and the bottom for receiver flask.

Supplied complete with Water Bath Digital and fitted with Digital RPM/Speed Meter.

Fitted with Motorized Auto Lift System which operates up or down on touch of a button.

Rotary Vacuum Evaporator Manufacturer, Rotary Vacuum Evaporator Suppliers, Rotary Vacuum Evaporator India, Rotary Vacuum Evaporator Exporter, Water Distillation Plant, buy Rotary Vacuum Evaporator, Rotary Vacuum Evaporator, Analytical Research Equipment, buy Rotary Vacuum Evaporator Online India

```
{ "@context": "http://schema.org/", "@type": "Product", "name": "Rotary Vacuum Evaporator",  
  "image": "https://www.jlabexport.com/images/catalog/product/1879869088rotary-vacuum-
```

evaporator.jpg", "description": "The apparatus consists of an evaporating flask rotated by heavy duty motor in a heating water bath. Fitted with speed regulator for minor speed adjustments. Vacuum distillation of solvent at high and low temperature is achieved quickly by use of a heavy duty motor, which prevents foaming and bumping of the liquid (solvent) into the evaporating flask and also distillation under controlled atmosphere. The evaporating flask is pear shaped to give a large surface area of evaporation. Evaporating flask is clamped to a glass duct which goes through the drive unit and protrudes about 120mm into the condenser.. Condenser is fitted with standard joint at the top and the bottom for receiver flask. Supplied complete with Water Bath Digital and fitted with Digital RPM/Speed Meter. Fitted with Motorized Auto Lift System which operates up or down on touch of a button. Rotary Vacuum Evaporator Manufacturer, Rotary Vacuum Evaporator Suppliers, Rotary Vacuum Evaporator India, Rotary Vacuum Evaporator Exporter, Water Distillation Plant, buy Rotary Vacuum Evaporator, Rotary Vacuum Evaporator, Analytical Research Equipment, buy Rotary Vacuum Evaporator Online India", "brand": "JLab Export", "sku": "5", "gtin8": "5", "gtin13": "5", "gtin14": "5", "mpn": "55", "aggregateRating": { "@type": "AggregateRating", "ratingValue": "5", "bestRating": "5", "worstRating": "0", "ratingCount": "5" } }
