

Product Code . JL-CE-6285



Auto Colorimeter Analyzer Battery Operated

Description

Auto Colorimeter Analyzer Battery Operated

8 filters with 16x2 lines LCD display for Automatic % transmission, optical Density & concentration measurements.

Soft touch type.

Memory of 3 standards to avoid frequent use of standards.

1 ml solution measurement.

Display 16x2 line alpha numeric LCD

Display Modes % T, AB & 3 concentration modes-C1,C2,C3

Zero Adjustment Automatic (Without Knob Rotation).

Accuracy:- ± 0.02 O.D

Stability:- ± 0.02 O.D per hour

Light Source 6.8 V , 0.3 amp , Tungsten lamp

Sample Volume 1 ml minimum

Amplifier Micro controller Based

Memory In built memory to retain three concentrations and last K factor for concentration even after power loss.

Accessories:-

Set of 5 Test Tube

Tube Stand

Spare Lamp

Dust Cover

Instruction Manual
